

NEW DVE™ Viscometer

our most affordable digital viscometer

New User Interface

- Keypad control
- Sharp viewing screen for close up or distance viewing

No Calculations Required

- Direct reading of viscosity

Displayed Info:

- Viscosity (cP, P, mPa•s or Pa•s)
- % Torque
- Speed/Spindle

Easy-to-Use

Range:

Push for determining full scale range (FSR) viscosity

18 Speeds

for complete range capability

Bubble Level

conveniently located for easy adjustment

Accuracy: ±1.0% of range

Repeatability: ±0.2%



What's Included?

- Instrument
- 6 spindles (RV/HA/HB) or 4 spindles (LV)
- Spindle Guard Leg*
- Lab Stand (Model A)
- Carrying Case

*Not applicable to HA or HB torque models

Optional Accessories

- Viscosity Standards
- RV/HA/HB-1 Spindle
- Quick Action Lab Stand
- Temperature Bath
- Small Sample Adapter
- UL Adapter
- Thermosel
- DIN Adapter
- Quick Connect/Extension Links

MODEL	VISCOSITY RANGE cP(mPa•s)		SPEEDS	
	Min.	Max.	RPM	Number of Increments
DVELV	1†	2M	.3-100	18
DVERV	100††	13M	.3-100	18
DVEHA	200††	26M	.3-100	18
DVEHB	800††	104M	.3-100	18

† 1 cP achieved with UL Adapter accessory. 15 cP on LV with standard spindles.

†† Minimum viscosity is achieved with optional RV/HA/HB-1 spindle.

M = 1 million cP = Centipoise mPa•s = Millipascal•seconds